



K I N T E K P R E S S

C o n t a c t u s f o r m o r e c a t a l o g s o f

KINTEK PRESS

> > >

KINTEK Press



C i p

: P C I M



K I N T E K

	PCI M- 12T	PCI M- 20T	PCI M- 40T	PCI M- 60T
	0 - 12T 0 - 17 MP a	0 - 20T 0 - 21 MP a	0 - 40T 0 - 30 MP a	0 - 60T 0 - 34 MP a
	95 mm (d)	110 mm (d)	130	150
(T)	40	40	50	50
	10 - 40	10 - 40	10 - 40	10 - 40
	0 - 300 MP a			
	22 × 70 mm(M× N)	30 × 120 mm(M× N)	40 × 150 mm(M× N)	50 × 150 mm(M× N)
	305 × 195 × 530 x x	305 × 195 × 600 x x	355 × 215 × 710 x x	405 × 240 × 720 x x
	90	100	130	180

1.7 [1.86 [25 [MP a
3.5 [3.72 [MP a	50 [
5 [5.57 [MP a	75 [
7 [7.43 [100 [
8.7 [9.29 [125 [
10.5 [11.2 [150 [
14 [14.8 [MP a	200 [
17.5 [18.6 [250 [
21 [22.3 [MP a	300 [

35 MP a

C i p

: P C I E



K I N T E K

	PCI E - 12T	PCI E - 20T	PCI E - 40T	PCI E - 60T
	0 - 12T 0 - 17 MPa	0 - 20T 0 - 21 MPa	0 - 40T 0 - 30 MPa	0 - 60T 0 - 34 MPa
	95 mm (d)	110 mm (d)	130	150
	0.0 - 40.0 MPa	0.0 - 40.0 MPa	0.0 - 40.0 MPa	0.0 - 40.0 MPa
(T)	40	40	50	50
	/	/	/	/
	/	/	/	/
	10 - 40	10 - 40	10 - 40	10 - 40
	0 - 300 MPa	0 - 300 MPa	0 - 300 MPa	0 - 300 MPa
	22 × 70 mm(M × N)	30 × 120 mm(M × N)	40 × 150 mm(M × N)	50 × 150 mm(M × N)
	305 × 430 × 530 × ×	305 × 430 × 600 × ×	355 × 450 × 710 × ×	405 × 470 × 720 × ×
	550W 220V / 110	550W 220V / 110	550W 220V / 110	550W 220V / 110
	110	120	150	200

C i p

: P C I A



(C I P)

K I N T E K

	PCI A - 20T	PCI A - 40T	PCI A - 60T	PCI A - 100T
	110 mm (d)	130	150	200
	- -	- -	- -	-- --
	4.3 LCD	4.3 LCD	4.3 LCD	7
	300 - 500MPA	300 - 500MPA	300 - 500MPA	300 - 500MPA
	30 × 150mm (M × N)	40 × 150mm (M × N)	50 × 150mm / 30 × 150mm	60 × 150 (M × N)
(T)	50	50	50	50
	240 × 390 × 560 x x	280 × 460 × 660 x x	/	330 × 580 × 720 x x
	550W 220V / 110	550W 220V / 110	550W 220V / 110	550W 220V / 110
	120	180	240	290

C i p

: P C E S I



K I N T E K

	PCESI - 65T	PCESI - 100T	PCESI - 150T	PCESI - 200T
	0 - 65T	0 - 100T	0 - 150T	0 - 200T
	160mm (d)	200mm (d)	200	290
	-	-		
	7			
	0 - 300 MP a	0 - 300 MP a	0 - 300 MP a	0 - 300 MP a
	50 × 150 mm(M× N)	60 × 150 mm(M× N)	80 × 150 mm(M× N)	90 × 150 mm(M× N)
(T)	50	50	50	50
	220 × 400 ×	260 × 400 ×	280 × 400 ×	290 × 420 ×
	700 × 450 × 1050 mm(L × W× H) 850 × 500 × 1100 mm(L × W× H) 950 × 550 × 1150 mm(L × W× H) 1000 × 650 × 1200 mm(L × W× H)			
	1500W 220V / 110V			
	350	580	680	980



K i n t e k P r e s s

89

W h a t s A p p

Image Not Found