



K I N T E K P R E S S

C o n t a c t u s f o r m o r e c a t a l o g s o f

KINTEK PRESS

> > >

KINTEK Press



: PCVM



KINTEK

	PCVM-10T		
	0-10.0		
	500° C		
	180x180	200x200	
	SUS 304		
	400x400x400		
	300x350		
	-0.1		
x x	450x550x850		
	220	50	110

: PCSM



KINTEK

	PCSM- 30T3030	PCSM- 40T4040
	0- 30. 0	0- 40. 0
	130 (d)	130 d
	- 300. 0C / 500. 0C	- 300. 0C
	[[
	300×300 M×N	400×400 M×N
	380×350×600 K×P×H	500×480×650 K×P×H
	700×400×600 x x	800×480×650 x x
	3000 W 220V / 110V	5000 W 220V / 110V
	260	460

: PCY



K I N T E K

	PCY - 5T1212	PCY - 10T1818	PCY - 10T2020	PCY - 15T3030
	0 - 5 . 0	0 - 10 . 0	0 - 10 . 0	0 - 15 . 0
	50 (d)	65mm (d)	65	95
	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C
	[[[[
	120×120mm(M×N)	180×180mm M×N	200×200mm M×N	300×300mm M×N
	140×140×60	180×180×60	200×200×60	300×300×65
	250×230×390 × ×	290×290×420 × ×	320×290×420 × ×	450×420×450 × ×
	700 220 / 110	1000 W 220V / 110V	1200 W 220V / 110V	3000 220V / 110V
	55	90	95	180

: CPCL



K I N T E K

	PC - 900 L
	0 - 5 . 0
	80
	1 000 ° C
	10 - 30
	50 x 90 mm
	60 mm
x x	400 x 380 x 780
	220 50

24T 30T 60T

: PCH



	PCH- 24T1010	PCH- 30T2020	PCH- 30T1818
	0 - 24 . 0	0 - 30 . 0	0 - 30 . 0
	95 (d)	110	150mm (d)
	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C	- 300 . 0C / 500 . 0C
	[[[
	100×100mm (M×N)	200×200 M×N	180×180 M×N
	245×175×500 K×P×H	405×260×525 K×P×H	405×260×525 K×P×H
	500×175×500 x x	950×260×525 x x	950×260×525 x x
	600 W 220V / 110V	1200 W 220V / 110V	1000 W 220V / 110V
	60	180	180

: PCV



K I N T E K

	PCV - 10T1818	PCV - 10T2020
	0 - 10.0	0 - 10.0
	500 ° C	500 ° C
	180 × 180	200 × 200
	SUS 304	SUS 304
	400 × 400 × 400	400 × 100 × 400
	300 × 350	300 × 350
	- 0.1 MPa	- 0.1
	450 × 550 × 850 × ×	450 × 550 × 850 × ×
	220V 50Hz 110V	220V 50Hz 110V

: PCSE



KINTEK

300 ° C

	PCSE - 40T4040	PCSE - 30T3030
	0-40.0	0-30.0
	-	-
	-300.0 ° C	-300.0 ° C / 500.0 ° C
	[[
	400 × 400 mm (M × N)	300 × 300 M × N
	500 × 480 × 650 K × P × H	380 × 350 × 600 K × P × H
	850 × 480 × 650 x x	700 × 400 × 600 x x
	5500 220 / 110	3500W 220V / 110V
	480	280

: P P L



K I N T E K

	PP - 900L
	0 - 10T
	- -
	1 ~ 9999 " "
	80
	1000
	10 - 30
	50 x 90 mm
	60 mm
	400 x 380 x 780 x x
	220 50

: PCAH



K I N T E K

	PCAH- 25T1818/1818G	PCAH- 25T2020/2020G	PCAH- 30T3030/3030G	PCAH- 40T4040/4040G
	0- 25. 0	0- 25. 0	0- 30. 0	0- 40. 0
	- -	- -	- -	- -
	- 300. 0 / 500. 0	- 300. 0 / 500. 0	- 300. 0 / 500. 0	- 300. 0
	[[[[
	180×180 x	200×200 x	300×300 x	400×400 x
	300×390×560 x x	300×390×560 x x	400×490×580 x x	500×550×620 x x
	1700 220 / 110	1700 220V/110V	3500 W 220V/110V	5500 220V/110V
	140	140	280	480

: P H A



K I N T E K

	P H A
	0 - 10 T
	- -
	1 ~
	80
	1000
	10 - 30
	50 * 90 mm
	60
	400 * 380 * 780 * *
	220 50



K i n t e k P r e s s

89

W h a t s A p p

Image Not Found