



K I N T E K P R E S S

C o n t a c t u s f o r m o r e c a t a l o g s o f

KINTEK PRESS

> > >

KINTEK Press



K b r

2 T

: K T - K B P



K I N T E K 2 T

K B r

	P C K B R - 2 T
(T)	0 - 2 (3 0 M p a)
	4 5 m m
	1 M P a / 1 0
	4 5 m m
×	5 4 × 5 5
× ×	1 0 0 × 2 2 0 × 2 2 0
	4 . 8

: PCMP



K I N T E K

	PCMP - 2 T	PCMP - 5 T	PCMP - 12 T	PCMP - 15 T	PCMP - 24 T	PCMP - 30 T	PCMP - 40 T
	0 - 2 T 25MPa	0 - 5 T 0 - 31.4M	0 - 12 T 0 - 30MF	0 - 15 T 0 - 30MI	0 - 24 T 0 - 34MI	0 - 30 T 0 - 31.5	0 - 40 T 0 - 30MPa
	32mm (d)	45mm (d)	70mm (d)	80mm (d)	95mm (d)	110mm (d)	130mm (d)
(T)	30	30	30	30	30	40	50
	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10
	50mm (D)	80mm (D)	80mm (D)	90mm (D)	105mm (D)	120mm (D)	140mm (D)
	85×120	96×130	96×130	140×150	80×150	92×160	106×185
				x			M×N
	210×150×350	225×155×380	225×155×380	245×175×390	245×175×415	275×195×420	295×215×500
	x x	x x	x x	x x	x x	x x	x x
	12	28	28	38	42	56	75

: PCF



KINTEK

	PCF - 15T	PCF - 24T	PCF - 30T	PCF - 40T	PCF - 60T
	0 - 15T 0 - 30MPa	0 - 24T 0 - 34MPa	0 - 30T 0 - 31.5MP	0 - 40T 0 - 30MPa	0 - 60T 0 - 34MPa
	80mm (d)	95mm (d)	110mm (d)	130mm (d)	150mm (d)
" (T)	30	30	40	50	50
	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10
	90mm (D)	105mm (D)	120mm (D)	140mm (D)	160mm (D)
	80××130 ×	112×160 ×	112×160 ×	126×185 ×	185×250 ×
	260×175×395 × ×	305×195×425 × ×	305×195×425 × ×	355×215×505 × ×	405×240×565 × ×
	42	65	65	90	120

1	0.75
3	2.2
5	3.7
10	7.5
12	9
15	11.3
20	15
30	22.5
40	30

: P T 1 0



	P T 1 0
	3 C r 1 3
	1 0 , 1 2 , 1 4 , 1 5 , 1 6 , 1 8 , 1 9 (d)
	1 2 0 * 2 0 0 * 2 8 0 * *
	1 0

: PC2NS



KINTEK
LR44

CR2032

	PC2NS
	0 - 2 T (0 - 25MPa)
	32 d
	0.00 - 40.00MPa
	CR20
	CR16 CR20 CR24 CR30
	0.8 - 1.2
	CR16 CR20 CR24 CR30
	0.4
	210*165*290mm (L X * W * H)
	12

: P C 2 N



CR 2 0 3 2 L R 4 4

	PC - 2 N
	0 - 2 T (0 - 2 5 M P a)
	3 2 d
	CR 2 0
	CR 1 6 CR 2 0 CR 2 4 CR 3 0
	0 . 8 - 1 . 2
	CR 1 6 CR 2 0 CR 2 4 CR 3 0
	0 . 4
	2 1 0 * 1 6 5 * 2 9 0 m m (L X * W * H)
	1 2

: P C B P



K I N T E K

PCBP - 2 T	PCBP - 1 . 5 T
0 - 2 T (0 - 25MPa)	50 - 1500
32mm (d)	- -
	0 - 999
CR20	4 . 3
CR16 , CR20 , CR24 , CR30 optional	CR16 CR20 CR24 CR30
0 . 8 - 1 . 2	CR16 CR20 CR24 CR30
CR16 CR20 CR24	CR20
	220x240x380 X X
210x165x290 x x	220 50 / 60
12	35

: PCEA



KINTEK

	PCEA - 12 T	PCEA - 20 T	PCEA - 30 T	PCEA - 40 T	PCEA - 60 T	PCEA - 100 T	PCEA - 150 T
	0 . 2 - 12 . 0	1 - 20 . 0	1 - 30 . 0	1 - 40 . 0	1 - 60 . 0	1 - 100 . 0	1 - 150 . 0
	4 . 3	7					
	100 , 000						
(T)	30	50					
M × N	110 × 140	140 × 160	140 × 160	175 × 180	185 × 220	185 × 250	200 × 260
× ×	185 × 320 × 360	230 × 390 × 42	230 × 390 × 42	280 × 460 × 55	300 × 520 × 58	330 × 580 × 62	400 × 620 × 620
	240W 220V / 110V	550W 220V / 110V				1500W 220V / 110V	
	50	90	150	180	240	380	

: PCES



KINTEK

	PCES - 40T	PCES - 65T	PCES - 100T	PCES - 150T	PCES - 200T
	0 - 40	0 - 65	1 - 100	1 - 150	1 - 200
	130	160	200	250	290
	7 LCD	7 LCD	7 LCD	7 LCD	7 LCD
	(50	50	50	50	50
	160×300 ×	220×300 ×	260×250 ×	285×290 ×	290×300 ×
	500×700×800 ×	580×700×800 ×	850×500×950 ×	950×600×1000mm (	1000×650×1050mm (L×W×H)
	1500 220 / 110	1500 220 / 110	1500 220 / 110	1500 220 / 11	1500 220 / 110
	200	280	520	620	850

X r f K b r

: P C P E



K I N T E K

	PCPE - 20 T	PCPE - 30 T	PCPE - 40 T	PCPE - 60 T
	0 - 20 T 0 - 28 MPa	0 - 30 T 0 - 31.5 MPa	0 - 40 T 0 - 30 MPa	0 - 60 T 0 - 33 MPa
	95mm (d)	110mm (d)	130mm (d)	150mm (d)
	0.00 - 40.00	0.00 - 40.00	0.00 - 40.00	0.00 - 40.00
(T)	30	40	50	50
	1MPa / 10	1MPa / 10	1MPa / 10	1MPa / 10
	/	/	/	/
	/	/	/	/
	105mm (D)	120mm (D)	140mm (D)	160mm (D)
	80×150 ×	92×160 ×	115×185 ×	185×250 ×
	245×415×415 × ×	275×430×420 × ×	295×450×500 × ×	405×470×565 × ×
	220 50 / 60	220 50 / 60	220V 50 / 60	220V 50 / 60
	58	72	92	140

1 [	1.41 [MPa
2 [	2.82 [MPa
3 [	4.23 [
5 [	7.06 [MPa
8 [	11.3 [
10 [	14.1 [
12 [	17 [

1 5 [	2 2 . 6 [
2 0 [	2 8 [
3 5	

: PP2N



KINTEK
300 - 600

	PP2N
	50 - 1500
	-
	0 - 999
	4.3
	CR16 CR20 CR24 CR30
	CR16 CR20 CR24 CR30
	CR20
	220*240*380 * *
	220 50 / 60
	35

X r f K b r

: PMXA



K i n T e k X R F

X R F / I R

	PMXA - 30 T	PMXA - 40 T	PMXA - 60 T
	1 - 30 . 0	0 - 40 . 0	0 - 60 . 0
	- - -	- - -	- - -
	0 - 999	0 - 999	0 - 999
	4 . 3	4 . 3	4 . 3
	100 , 000	100 , 000	100 , 000
	/ / 1	/ / 1	/ / 1
	40 mm	40 mm	40
	440 C	440 C	440 C
x x	250×390×460	280×460×550	300×520×580
	550W 220V / 110V	550W 220V / 110V	550W 220V / 110V
	120	150	180

: P C G



	PCG - 25T1818	PCG - 25T2020
	0 - 25 T	0 - 25 T
	-	-
	0 - 999 . 59	0 - 999 . 59
	500	500
	180 × 180	200 × 200
	304	304
	780 × 650 × 700	780 × 650 × 700
	240 × 260 mm	240 × 260 mm
	- 0 . 1 MPa	- 0 . 1 MPa
	1200 × 950 × 1800 × ×	1200 × 950 × 1800 × ×
	220 50	220 V 50 Hz



K i n t e k P r e s s

8 9

W h a t s A p p