

24T 30T 60T

: PCH



	PCH-24T1010	PCH-30T2020	PCH-30T1818
	0-24.0	0-30.0	0-30.0
	95 (d)	110	150mm (d)
	-300.0C/500.0C	-300.0C/500.0C	-300.0C/500.0C
	[	[	[
	100×100mm (M×N)	200×200 M×N	180×180 M×N
	245×175×500 K×P×H	405×260×525 K×P×H	405×260×525 K×P×H
	500×175×500 × ×	950×260×525 × ×	950×260×525 × ×
	600 W 220V/110V	1200 W 220V/110V	1000 W 220V/110V
	60	180	180