

: PCSE



K I N T E K

3 0 0 ° C

	PCSE - 40T4040	PCSE - 30T3030
	0 - 40 . 0	0 - 30 . 0
	- -	- -
	- 300 . 0 ° C	- 300 . 0 ° C / 500 . 0 ° C
	[	[
	400×400mm (M×N)	300×300 M×N
	500×480X650 K×P×H	380×350×600 K×P×H
	850×480X650 × ×	700×400×600 × ×
	5500 220 / 110	3500W 220V / 110V
	480	280