

: PCAH



K I N T E K

	PCAH-25T1818/1818G	PCAH-25T2020/2020G	PCAH-30T3030/3030G	PCAH-40T4040/4040G
	0-25.0	0-25.0	0-30.0	0-40.0
	- -	- -	- -	- -
	-300.0 / 500.0	-300.0 / 500.0	-300.0 / 500.0	-300.0
	[	[	[	[
	180×180 ×	200×200 ×	300×300 ×	400×400 ×
	300×390×560 × ×	300×390×560 × ×	400×490×580 × ×	500×550×620 × ×
	1700 220 / 110	1700 220V/110V	3500 W 220V/110V	5500 220V/110V
	140	140	280	480