

C i p

: P C I A



(C I P)

K I N T E K

	PCIA-20T	PCIA-40T	PCIA-60T	PCIA-100T
	110 mm (d)	130	150	200
	- -	- -	- -	- -
	4.3 LCD	4.3 LCD	4.3 LCD	7
	300 - 500MPA	300 - 500MPA	300 - 500MPA	300 - 500MPA
	30 × 150mm (M × N)	40 × 150mm (M × N)	50 × 150mm / 30 × 150mm	60 × 150 (M × N)
(T)	50	50	50	50
	240 × 390 × 560 × ×	280 × 460 × 660 × ×	/	330 × 580 × 720 × ×
	550W 220V / 110	550W 220V / 110	550W 220V / 110	550W 220V / 110
	120	180	240	290