

: PMH



KINTEK
500 °C

	- 300.0 °C 500 °C
	440C
	HRC60 - HRC62
	€ 10 , € 13 , € 15 , € 20 , € 30 , € 40mm
	40 N
	€ 78 * 138mm , € 90 * 138mm (*)
	300 W 220V / 110V
	9

[Mpa	50	100	300	400	600	800	1000	1200	1500
€ 8 T	0.25	0.5	1.5	2.01	3.01	4.02	5.02	6.03	7.53
€ 10 T	0.39	0.78	2.35	3.14	4.71	6.28	7.85	9.42	11.7
€ 12 T	0.56	1.13	3.39	4.52	6.78	9.04	11.3	13.5	16.9
€ 13 T	0.66	1.32	3.98	5.3	7.96	10.6	13.2	15.9	19.9
€ 15 T	0.88	1.76	5.3	7.06	10.6	14.1	17.6	21.2	26.5
€ 20 T	1.57	3.14	9.42	12.5	18.8	25.1	31.4	37.6	47.1