

## C i p

: P C I E



K I N T E K

	P C I E - 12 T	P C I E - 20 T	P C I E - 40 T	P C I E - 60 T
	0 - 12 T 0 - 17 MP a	0 - 20 T 0 - 21 MP a	0 - 40 T 0 - 30 MP a	0 - 60 T 0 - 34 MP a
	95 mm ( d )	110 mm ( d )	130	150
	0 . 0 - 40 . 0 MP a	0 . 0 - 40 . 0 MP a	0 . 0 - 40 . 0 MP a	0 . 0 - 40 . 0 MP a
( T )	40	40	50	50
	/	/	/	/
	/	/	/	/
	10 - 40	10 - 40	10 - 40	10 - 40
	0 - 300 MP a	0 - 300 MP a	0 - 300 MP a	0 - 300 MP a
	22 × 70 mm( M × N )	30 × 120 mm( M × N )	40 × 150 mm( M × N )	50 × 150 mm( M × N )
	305 × 430 × 530 × ×	305 × 430 × 600 × ×	355 × 450 × 710 × ×	405 × 470 × 720 × ×
	550 W 220 V / 110	550 W 220 V / 110	550 W 220 V / 110	550 W 220 V / 110
	110	120	150	200