

C i p

: P C E S I



K I N T E K

	PCESI - 65T	PCESI - 100T	PCESI - 150T	PCESI - 200T
	0 - 65 T	0 - 100 T	0 - 150 T	0 - 200 T
	160 mm (d)	200 mm (d)	200	290
	-	-		
	7			
	0 - 300 MPa	0 - 300 MPa	0 - 300 MPa	0 - 300 MPa
	€ 50 × 150 mm (M × N)	€ 60 × 150 mm (M × N)	€ 80 × 150 mm (M × N)	€ 90 × 150 mm (M × N)
(T)	50	50	50	50
	220 × 400 ×	260 × 400 ×	280 × 400 ×	290 × 420 ×
	700 × 450 × 1050 mm (L × W × H)	850 × 500 × 1100 mm (L × W × H)	950 × 550 × 1150 mm (L × W × H)	1000 × 650 × 1200 mm (L × W × H)
	1500W	220 V / 110 V		
	350	580	680	980