

X r f K b r

: P C P E



K I N T E K

	PCPE - 20T	PCPE - 30T	PCPE - 40T	PCPE - 60T
	0 - 20T 0 - 28 MPa	0 - 30T 0 - 31.5 MPa	0 - 40T 0 - 30 MPa	0 - 60T 0 - 33 MPa
	95 mm ( d )	110 mm ( d )	130 mm ( d )	150 mm ( d )
	0.00 - 40.00	0.00 - 40.00	0.00 - 40.00	0.00 - 40.00
( T )	30	40	50	50
	1 MPa / 10	1 MPa / 10	1 MPa / 10	1 MPa / 10
	/	/	/	/
	/	/	/	/
	105 mm ( D )	120 mm ( D )	140 mm ( D )	160 mm ( D )
	80 x 150 x	92 x 160 x	115 x 185 x	185 x 250 x
	245 x 415 x 415 x x	275 x 430 x 420 x x	295 x 450 x 500 x x	405 x 470 x 565 x x
	220 50 / 60	220 50 / 60	220V 50 / 60	220V 50 / 60
	58	72	92	140

1 [	1.41 [ MPa
2 [	2.82 [ MPa
3 [	4.23 [
5 [	7.06 [ MPa
8 [	11.3 [
10 [	14.1 [
12 [	17 [

15 [	22.6 [
20 [	28 [
35	