

: P C S M



K I N T E K

	PCSM - 30T3030	PCSM - 40T4040
	0 - 30 . 0	0 - 40 . 0
	130 (d)	130 d
	- 300 . 0 C / 500 . 0 C	- 300 . 0 C
	[	[
	300 × 300 M × N	400 × 400 M × N
	380 × 350 × 600 K × P × H	500 × 480 × 650 K × P × H
	700 × 400 × 600 x x	800 × 480 × 650 x x
	3000 W 220 V / 110 V	5000 W 220 V / 110 V
	260	460