

C i p

: P C I M



K I N T E K

	PCIM-12T	PCIM-20T	PCIM-40T	PCIM-60T
	0-12T 0-17MPa	0-20T 0-21MPa	0-40T 0-30MPa	0-60T 0-34MPa
	95mm (d)	110mm (d)	130	150
(T)	40	40	50	50
	10 - 40	10 - 40	10 - 40	10 - 40
	0-300MPa	0-300MPa	0-300MPa	0-300MPa
	22×70mm (M×N)	30×120mm (M×N)	40×150mm (M×N)	50×150mm (M×N)
	305×195×530 × ×	305×195×600 × ×	355×215×710 × ×	405×240×720 × ×
	90	100	130	180

1.7 [	1.86 [	25 [MPa
3.5 [	3.72 [MPa	50 [
5 [	5.57 [MPa	75 [
7 [	7.43 [	100 [
8.7 [	9.29 [	125 [
10.5 [	11.2 [	150 [
14 [	14.8 [MPa	200 [
17.5 [	18.6 [	250 [
21 [	22.3 [MPa	300 [

35MPa