

: PCI H



KINTEK (WIP)  
ASME  
50 - 100 ° C

	PCI H- 20T	PCI H- 40T	PCI H- 60T	PCI H- 100T
	0 - 20T	0 - 40T	0 - 60. 0	0 - 100
	130	150	200	220
	1 999	1 999	1 999	1 999
	7	7	7	7
	- 200. 0C	- 200. 0C	- 200. 0C	- 200. 0
	300	300MPa	300MPa	500MPa
	30×150mm( M×N)	40×150mm( M×N)	×50×150 ( M×N)	×50×150 ( M×N)
( T )	50	50	50	50